



Uninsulated Fork Terminal For 16 - 14 AWG

By Burndy
Catalog Number [YAV14T32FBOX](#)



Copper Compression Lug, Heavy Duty, Fork Tongue, w/ Inspection Hole, 20-14 AWG, #4-#6 Stud, Short Barrel, Tin Plated, Wire strip length: 9/32".

General

Application	For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Fork Tongue
UPC	781810534038
UPC 12 Digit	7818105340388

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.27 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - D inch	0.48 in
Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.84 in
Dimension - N inch	0.23 in
Dimension - Outside Diameter inch	0.16 in
Dimension - Pad Width inch	0.30 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#4;#5;#6
Dimension - Z inch	0.25 in

Conductor Related

Conductor - Copper Str Aircraft Size	AN 20;AN 18;AN 16;AN 14
Conductor - Copper Str Aircraft Size Range	AN 20-AN 14
Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG;14 AWG
Conductor - Copper Str Size Range	20 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Pallet Quantity	99999

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50094187](#)
- [Technical Solutions - BURNDY_YAV14T32FBOX_Specsheet](#)



A proud member of the Hubbell Family.

