

KK3A40U4N, AL Universal Terminal, 3 Conductor, 350-800 kcmil, 4-Hole, 1/2" Stud, 1.75" Spacing, 6 Screws, Al/Cu Rated



By Burndy
Catalog # [KK3A40U4N](#)

Aluminum Universal Terminal, 3 Conductor, 4 Hole, 350-800 kcmil, 1/2" Stud, 1.75" Stud Hole Spacing, 6 Screws, Al/Cu Rated, Tin Plated.

Features

- Dual rated panelboard lugs constructed from high strength extruded aluminum alloy, electro tin-plated to provide low contact resistance

Application

For Aluminum and Copper Conductors

General

Catalog Number	KK3A40U4N
Connector Type	Parallel Set-Screw
EU RoHS Indicator	No
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNIVERSAL TERMINAL
Type	Bolted Lugs & Terminals
UPC	781810370476

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	1.89 in
Dimension - Height mm	48 mm
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	157 mm
Dimension - Length Overall inch	6.19 in
Dimension - N inch	0.63 in

Dimension - Pad Width inch	5.34 in
Dimension - Stud Size inch	0.56 in

Conductor Related

Conductor - AL Str Size	300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Size Range	300-800 Kcmil
Conductor - Copper Str Size Range	300-800 Kcmil
Conductor Size	350-800 KCMIL
Conductor Type	<ul style="list-style-type: none"> CU C Str-Size AL C Str-Size
Number Of Wires	3
Number of Conductors	3

Certifications And Compliance


Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Product Assets

- [3D Models - KK3A40U4N_MODEL-STEP](#)
- [3D Models - KK3A40U4N_MODEL-PDF](#)
- [3D Models - KK3A40U4N_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR_KK3A-U_LineArt
Sales Drawings - se210997
Specifications - KK3A40U4N



©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-KK3A40U4N-SPEC-EN | REV 10/2024