



Compression Terminal

By Burndy
Catalog # [YAV1502M12](#)

Non Insul Cu Comp Tubular Terminal, Metric, 2
Hole/W/InspWindow, 150 mm, M12 Stud, Tin-Electro Plated, 17
Index.



Application

Metric Wire Termination

General

Catalog Number	YAV1502M12
Connector Type	METRIC
Die Index	17
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810442739
UPC 12 Digit	7818104427399

Dimensions

Dimension - B Length fraction	1-3/50 in
Dimension - B Length inch	26.2 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	2.66 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	113 mm
Dimension - Length Overall inch	4.45 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	30.5 in
Dimension - Strip Length inch	1.06 in
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	150 mm ²
Conductor - Copper Str Size Range	300 kcmil
Conductor - Material	COPPER
Conductor Size	150 mm ²
Conductor Type	CLASS 2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[3D Models - YAV1502M12_MODEL-PDF](#)
[3D Models - YAV1502M12_MODEL-IGES](#)
[3D Models - YAV1502M12_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
[Sales Drawings - 50025887](#)



A proud member of the Hubbell Family.