

## KS15, Split Bolt Connector, Run/Tap: #10-8 AWG Str

By Burndy  
Catalog # KS15



Copper Split Bolt, Cu: 10-8 AWG (Str) (Run & Tap).

### Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

### Application

For Direct Burial Applications In Earth Or Concrete, Copper

### General

Catalog Number	KS15
Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque	80 in-lbs
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810011256
UPC 12 Digit	7818100112566

### Dimensions

Dimension - B Length fraction	9/20 in
Dimension - B Length inch	.45 in
Dimension - Cross Flats inch	0.50 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.85
Dimension - Width fraction	19/50 in
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm
Width	0.38 in

### Conductor Related

Conductor - Copper Solid Run	8 AWG
Conductor - Copper Solid Run Range	10 AWG-8 AWG

Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Solid Tap Range	14 AWG-8 AWG
Conductor - Copper Str Run	10 AWG;9 AWG;8 AWG
Conductor - Copper Str Run Range	10 STR - 8 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Tap Range	10 STR - 8 STR
Conductor - CopperWeld Solid Tap	#8
Conductor - CopperWeld Solid Tap Range	#8
Conductor - CopperWeld Str Run	#8
Conductor - CopperWeld Str Run Range	#8
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• CU Weld C Solid-Run</li> <li>• CU Weld C Str-Run</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Solid-Tap</li> <li>• CU Weld C Str-Tap</li> <li>• CU C Solid-Tap</li> </ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL486</li> <li>• UL467</li> <li>• CSA C22.2 No 41</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL486</li> <li>• UL467</li> <li>• CSA C22.2 No 41</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity 100  
Pallet Quantity 99000

**Product Assets**

3D Models - KS15\_MODEL-IGES  
3D Models - KS15\_MODEL-PDF  
3D Models - KS15\_MODEL-STEP  
Catalogs - BURNDY Master Catalog - Section A - Mechanical

Catalogs - BURNDY Master Catalog - Section E2 - Mechanical  
Grounding  
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog  
Customer Notices - Prop 65 Notice  
Interactive Catalog - BURNDY Full-Line Digital Catalog  
Product Cross Section Image(s) - BUR\_KS\_Lineart\_BW  
Sales Drawings - SD..078561-01  
Sell Sheets - SERVIT® Split-bolt Connectors  
Specifications - KS15



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_MX-KS15-SPEC-EN | REV 10/2024