



Uninsulated Ring Terminal For 6 AWG

By Burndy
Catalog Number [YAV6CL10BOX](#)

Seamless Uninsulated Compression Heavy Duty Ring Tongue Terminal #22-10 Stranded and Solid Copper.



General

Connector Type	Ring Terminal
Die Index	39
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none">DLP CopperTin Plating
Military Specification	MS20659
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810539200
UPC 12 Digit	7818105392000

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.47 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	0.86 in
Dimension - Hole Size inch	0.52 in
Dimension - Hole Size mm	13 mm
Dimension - Length Overall inch	1.64 in
Dimension - N inch	0.38 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Pad Width inch	0.74 in
Dimension - Strip Length inch	1/2 in
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.49 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Aircraft Size	AN 6
Conductor - Copper Str Aircraft Size Range	AN 6
Conductor - Copper Str Size	6
Conductor - Copper Str Size Range	6
Conductor Size	6 AWG
Conductor Type	<ul style="list-style-type: none">CU C Solid-SizeCU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL467Military Specified (Mil-Spec)
Standards - Industry Standards Met	UL467; Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Sales Drawings - 50094161_E](#)
[Technical Solutions - BURNDY_YAV6CL10BOX_Specsheet](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY_CA-YAV6CL10BOX-SPEC-EN | REV 11/2023