

Compression Terminal

By Burndy
Catalog # [YAV95FM16](#)

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 95 mm, 16 mm Stud, 2.84 IN L, Compression, 14 Index, 27 mm Strip Length.



Application

Metric Wire Termination

General

Catalog Number	YAV95FM16
Connector Type	METRIC
Die Index	14
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810324097
UPC 12 Digit	7818103240977

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.63
Dimension - D inch	1.24 in
Dimension - Hole Size fraction	5/8
Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	18 mm
Dimension - Inside Diameter inch	0.56 in
Dimension - L Length Overall mm	72.1 mm
Dimension - Length Overall inch	2.84 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Pad Width inch	1.03 in
Dimension - Strip Length inch	1.06 in
Dimension - Stud Size fraction	5/8
Dimension - Z (inch)	0.67 in
Physical Attribute - Tongue	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Material	COPPER
Conductor Size	95 mm ²
Conductor Type	CLASS 5

Certifications And Compliance

Standards - RoHS Compliance CM Status

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[3D Models - YAV95FM16_MODEL-PDF](#)
[3D Models - YAV95FM16_MODEL-STEP](#)
[3D Models - YAV95FM16_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
[Sales Drawings - 50025612](#)



A proud member of the Hubbell Family.