



YCA262NTN, Copper compression terminal, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Tin Plated

By Burndy
Catalog # [YCA262NTN](#)



Cu Compression terminal Designed for terminating Cu Conductors to switch pads, 2/0 Str., 1/2 IN Stud, 2 Pad holes, Tin plating.

General

Connector Type	Terminal
Die Index	166;206
Material	Copper
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810216026

Dimensions

Dimension - B Length fraction	1-18/25 in
Dimension - B Length inch	1.72 in
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	134 mm
Dimension - Length Overall inch	5.27 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.71 in
Dimension - Pad Width inch	0.97 in
Dimension - Strip Length inch	1 3/16
Dimension - Stud Size inch	1/2
Dimension - Z (inch)	0.62 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size 2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Pallet Quantity	5800

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - sd029071-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YCA262NTN-SPEC-EN | REV 6/2024