



YCA292NTN, Cu Compression Lug, 2-Hole, 1/2" Stud, 1-3/4" Spacing, 250 kcmil

By Burndy
Catalog # [YCA292NTN](#)



Cu Wire lug, 250 kcmil, .56"stud, 5.52"L.

General

Catalog Number	YCA292NTN
Connector Type	Terminal
Die Index	169
Material	Copper
Oxide Inhibitor Type	Penetrox A
Physical Attribute - Number of Crimps Required	1
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810413005

Dimensions

Dimension - B Length fraction	1- 81/100 in
Dimension - B Length inch	1.81 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	140 mm
Dimension - Length Overall inch	5.52 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.28 in
Dimension - Strip Length inch	1 7/8
Dimension - Stud Size inch	33/64
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	20
Pallet Quantity	2960

Product Assets

[3D Models - YCA292NTN_MODEL-IGES](#)
[3D Models - YCA292NTN_MODEL-STEP](#)
[3D Models - YCA292NTN_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - SD..029071-01](#)



A proud member of the Hubbell Family.