

KVSU34, Mechanical Connector with Spacer Bar

By Burndy
Catalog # KVSU34

Tin-plated copper alloy connector with tin plated silicon bronze hardware. Spacer bar separates dissimilar conductors and provides long contact length, Tightening torque: 375 in-lb, wrench size: 3/4 cross flats.

Features

- Compact, tin-plated high strength copper alloy connector with spacer and tin-plated silicon bronze hardware
- Recommended for heavy duty connections
- Spacer separates dissimilar conductors and provides long contact length
- Neoprene ring prevents loss of shorter bolt during installation
- Longer peened bolt permits swivel action for easier installation

Application

For All Combinations Of Copper, Aluminum, ACSR, AAAC And 5005

General

Catalog Number	KVSU34
EU RoHS Indicator	Yes
Sub Brand	OKLIP



Type	KVS, Compact, Universal
UPC	781810083307

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sd054222-01](#)
[Specifications - KVSU34](#)
[Specifications - BURNDY_KVSU34_Specsheet](#)