
YFTW1212DL, Covered Twin Ferrule, 12 AWG, Funnel Entry



By Burndy
Catalog # YFTW1212DL

Covered Twin Ferrule, 12 AWG, Electrolytic Copper, Tin Plated, Smooth Funnel Entry, No Fraying of Strands

Features

- Made of electrolytic copper, tin plated
- Smooth funnel entry to make wire insertion easier
- Secure contacting even after multiple reconnecctions
- Long-term contact resistance
- No fraying of strands
- No breakage of wire strands when wire is bent, under stress, or in vibration environment
- UL listed per UL486F requirements
- RoHS Compliant

Application

For Use On Copper Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	12 AWG
Conductor - Copper Solid Size	12 AWG
Conductor - Copper Str Size	12 AWG

Configuration

Connector Type	End Termination

Dimensions

Dimension - D1 inch	0.15 in
Dimension - D2 inch	0.35 in
Dimension - D inch	0.16 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall inch	0.91 in

General

Product Type	Ferrule
Plated	Yes
Product Family	COMPRESSION
UPC	621945623118
Type	Bootlace Ferrule
Insulation	Y
Sub Brand	FERRULES
Material	Copper
Plating Type	Tin

Logistics

Minimum Pack Quantity	100
Carton Quantity	1

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved