



YG14B2TC2C2C Compression Bus Bar Connector

By Burndy
Catalog # [YG14B2TC2C2C](#)



Bus Bar Copper Alloy Connector, #2 AWG.

Application

For Direct Barial And Cellular Tower Applicatons And Is Easier To Use Than Exothermic Connections

General

Catalog Number	YG14B2TC2C2C
Connector Type	Tap
EU RoHS Indicator	Yes
Material	Copper Alloy
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYGROUND
Trade Name	HYGROUND®
Type	YG-B
UPC	781810232712
UPC 12 Digit	7818102327122

Dimensions

Dimension - B Length fraction	64/79 in
Dimension - B Length inch	0.81 in
Dimension - Bus Bar Size Tap Side inch	1/4" Thick Busbar

Conductor Related

Conductor - Copper Solid Size A	2 AWG
Conductor - Copper Solid Size A Range	2 AWG
Conductor - Copper Solid Size B	2 AWG
Conductor - Copper Solid Size B Range	2 AWG
Conductor - Copper Str Size A	2 AWG
Conductor - Copper Str Size A Range	2 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size• Bar-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• UL 486A• CSA C22.2 No 65
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	20
Pallet Quantity	6960

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section E1 - Compression Grounding](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YG-B_LineArt](#)
[Sales Drawings - SC212090-01](#)





A proud member of the Hubbell Family.

BRDY_CA-YG14B2TC2C2C-SPEC-EN | REV 6/2024