


KVSW34, Mechanical Connector with Spacer Bar

By Burndy
Catalog # [KVSW34](#)



Mechanical Connector For CUWeld and Copper Supplied with a CU alloy Spacer that separates run and tap conductors, Recommended Torque: 375 LBS.

Application

For Copper And Copperweld Conductors

General

Catalog Number	KVSW34
EU RoHS Indicator	Yes
Installation Torque	480 LBS/in
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	OKLIP
Trade Name	OKLIP™
Type	KVSW
UPC	781810067307
UPC 12 Digit	7818100673077

Dimensions

Dimension - Height inch	3.06 in
Dimension - Height mm	77.72 mm
Dimension - Length Overall inch	1.34 in
Dimension - Stud Size inch	1/2 in
Dimension - Width inch	2.20 in

Conductor Related

Conductor - Copper Str Run	400 kcmil;450 kcmil;500 kcmil
----------------------------	-------------------------------

Conductor - Copper Str Run Range	400 kcmil - 500 kcmil
Conductor - Copper Str Tap	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Tap Range	4 str. - 500 kcmil
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_KVSW_LineArt](#)
- [Sales Drawings - sd009323-01](#)
- [Specifications - KVSW34](#)
- [Specifications - BURNDY_KVSW34_Specsheet](#)