



YGF292N Grounding Plate, #2 AWG-250 kcmil Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YGF292N](#)



Copper Compression Grounding Plate, 2 AWG - 250 kcmil, 1/2"
Stud, 1-3/4" Stud Hole Spacing.

Application

Used to position the grounding plate on a threaded rod prior to placement of the concrete.

General

Catalog Number	YGF292N
Die Index	997
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Tapped Holes	2
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	GROUNDING PLATE
Trade Name	HYGROUND®
Type	YGF
UPC	781810220504
UPC 12 Digit	7818102205044

Dimensions

Dimension - D inch	3.25 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	3-31/50 in
Dimension - Height inch	3.62 in
Dimension - L Length Overall mm	147 mm
Dimension - Length Overall inch	5.78 in
Dimension - Pad Width inch	2.00 in
Dimension - Thread Size	3/8 -16
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	2 AWG-250 kcmil
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	NEMA Size Holes
Standards - Industry Standards Met	UL467;IEEE 837
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Product Assets

[3D Models - YGF292N_MODEL-STEP](#)
[3D Models - YGF292N_MODEL-IGES](#)
[3D Models - YGF292N_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YGF_Lineart](#)
[Sales Drawings - sd082518-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-YGF292N-SPEC-EN | REV 6/2024