



# Full Cycle Ratchet Crimper, #22-10 AWG Uninsulated (bare) Terminals and Splices

By Burndy  
Catalog # [MR20](#)



Full Cycle Ratchet Crimper, #22-10 AWG Bare.

## Application

Crimping

## General

|                          |                                   |
|--------------------------|-----------------------------------|
| Application - For Use On | Uninsulated Terminals and Splices |
| Catalog Number           | MR20                              |
| Die Type                 | Permanent Die Grooves             |
| EU RoHS Indicator        | Yes                               |
| Tool Type                | Full Cycle Ratchet Crimper        |
| Trade Name               | HYTOOL™                           |
| UPC                      | 781810011195                      |
| UPC 12 Digit             | 7818100111955                     |

## Dimensions

|            |                             |
|------------|-----------------------------|
| Dimensions | 8.88 in x 6.00 in x 2.50 in |
| Height     | 2.5 in                      |
| Length     | 8.88 in                     |
| Weight     | 1.1 lb                      |
| Width      | 6 in                        |

## Conductor Related

Crimping Ranges #22 - #10 AWG

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Carton Quantity 20  
Package Contents Tool only

## Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Installation Manuals - MR15 MR18, MR20 Operating Manual](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_082\\_OTXF\\_MR15\\_MR18\\_MR20\\_lineart](#)  
[Sales Drawings - 10113613](#)  
[Specifications - MR20](#)