

PENA138, Oxide Inhibitor, 8 ounce

By Burndy
Catalog # PENA138

Oxide Inhibiting Electrical Joint Compound, 8 OZ, For Al-Al, Al-Cu & Al Conduit Threads / Insulated Cable.



Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

Application

Aluminum to Aluminum, Aluminum to Conduit, Aluminum to Copper

General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	PENA138
Container Type	Squeeze Bottle
EU RoHS Indicator	Yes
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
Type	Sealing compound
UPC	781810592571

UPC 12 Digit 781810592571
Viscosity at 100 Fahrenheit 250 °F

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	12
Container Size	8 oz
Pallet Quantity	1680

Product Assets

[3D Models - PENA138_MODEL-IGES](#)
[3D Models - PENA138_MODEL-PDF](#)
[3D Models - PENA138_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_PENA13_Lineart](#)
[Sales Drawings - SC087706-01](#)
[SDS - PENETROX A-13 FRENCH SDS](#)
[SDS - PENETROX A-13 SDS](#)
[SDS - PENETROX A-13 ESPANOL SDS](#)
[SDS - PENETROX A-13 GERMAN SDS](#)
[SDS - PENETROX A-13 ITALIAN SDS](#)
[SDS - PENETROX A-13 PORTUGUESE SDS](#)
[Specifications - PENA138](#)