



Heat Shrink Ring Terminal For 22 - 18 AWG

By Burndy
Catalog # [YHSA18K6](#)



Cu Heat Shrink Terminal, Ring Tongue, 18-22 AWG, #6 Stud, 1.18" L, 0.29" W, Serrated bbl, Tin plated, For Use On Cu Cond.

Application

For Use On Copper Conductor

General

Catalog Number	YHSA18K6
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Heat Shrink
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC	781810476925

Dimensions

Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Bolt Size fraction	#6
Dimension - Hole Size fraction	1/7
Dimension - Hole Size inch	0.14 in
Dimension - Hole Size mm	4 mm
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.14 in
Dimension - Pad Width inch	0.29 in
Dimension - Strip Length inch	5/16
Dimension - Stud Size inch	#6

Conductor Related

Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Packaging Type	Bag

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Product Cross Section Image\(s\) - BUR_YHSA18K6_LineArt](#)
[Sales Drawings - 50094158](#)



A proud member of the Hubbell Family.