



## PENA13CARTRIDGE, Oxide Inhibitor, Cartridge

By Burndy

Catalog # [PENA13CARTRIDGE](#)



Cartridge for PENETROX A-13.

### Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

### Application

For Aluminum To Copper, Aluminum To Aluminum, Aluminum To Conduit

### General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	PENA13CARTRIDGE
Container Type	Cartridge
EU RoHS Indicator	Yes
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F

Trade Name	PENETROX™
Type	A13
UPC	781810365519
UPC 12 Digit	7818103655199
Viscosity at 100 Fahrenheit	250 °F

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Container Size	1 lb
----------------	------

### Product Assets

[Catalogs - BURNDY Master Catalog - Section F - Accessories](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_PENA13QT\\_LineArt](#)  
[Sales Drawings - 50008001](#)  
[SDS - PENETROX A-13 FRENCH SDS](#)  
[SDS - PENETROX A-13 SDS](#)  
[SDS - PENETROX A-13 ESPANOL SDS](#)  
[SDS - PENETROX A-13 GERMAN SDS](#)  
[SDS - PENETROX A-13 ITALIAN SDS](#)  
[SDS - PENETROX A-13 PORTUGUESE SDS](#)  
[Specifications - PENA13CARTRIDGE](#)