

## PENE8, Oxide Inhibitor, 8 ounce

By Burndy  
Catalog # [PENE8](#)

Oxide Inhibiting Electrical Joint Compound, 8 OZ, For Cu-Cu, Cu Conduit Threads & Grounding Applications.



### Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

### Application

Copper to copper applications

### General

Application - For Use On	Copper to Copper
Catalog Number	PENE8
Container Type	Squeeze Bottle
EU RoHS Indicator	Yes
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
Type	Sealing compound
UPC	781810592854
UPC 12 Digit	7818105928544
Viscosity at 100 Fahrenheit	250 °F

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	12
Container Size	8 oz
Pallet Quantity	2400

### Product Assets

- [3D Models - PENE8\\_MODEL-STEP](#)
- [3D Models - PENE8\\_MODEL-PDF](#)
- [3D Models - PENE8\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_PENE8\\_LineArt](#)
- [Sales Drawings - SC087710-01](#)
- [SDS - PENETROX E PORTUGUESE SDS](#)
- [SDS - PENETROX E GERMAN SDS](#)
- [SDS - PENETROX E Polish SDS](#)
- [SDS - PENETROX E FRENCH SDS](#)
- [SDS - PENETROX E RUSSIAN SDS](#)
- [SDS - PENETROX E ESPANOL SDS](#)
- [SDS - PENETROX E SDS](#)
- [Specifications - PENE8](#)