




## Radiation Resistant Insulated Splice For 16 - 14 AWG

By Burndy  
Catalog # [YSES14K](#)



RADIATION RESISTANT INSULATED BUTT SPLICE,  
POLYVINYLDENE FLOURIDE (PVF2) INSULATED.

### General

Catalog Number	YSES14K
Color Code	Blue
Connector Type	Seamless Butt Splice
Insulation	Y
Insulation Type	Kynar
Material	Copper
Plated	Y
Plating Type	Tin
Temperature Rating	150
Trade Name	INSULINK™
Type	Radiation Resistant KYNAR Splice
UPC	781810085776
UPC 12 Digit	7818100857766

### Dimensions

Cable Insulation Diameter Maximum	0.153 in
Dimension - B Length fraction	15/79 in
Dimension - B Length inch	0.19 in
Dimension - Diameter Max Size inch	0.15 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in
Dimension - N inch	0.16 in
Dimension - Outside Diameter inch	0.25 in
Dimension - P inch	0.04 in
Dimension - Pad Width inch	0.15 in
Dimension - Strip Length inch	3/16 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Solid Size	16;15;14
Conductor - Copper Solid Size Range	16-14
Conductor - Copper Str Aircraft Size	AN 16;AN 14
Conductor - Copper Str Aircraft Size Range	AN 16-AN 14
Conductor - Copper Str Size	16;14
Conductor - Copper Str Size Range	16-14
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1000
Pallet Quantity	99999

### Product Assets

[3D Models - YSES14K\\_MODEL-IGES](#)  
[3D Models - YSES14K\\_MODEL-STEP](#)  
[3D Models - YSES14K\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section B - Small Compression](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094196](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-YSES14K-SPEC-EN | REV 6/2024

