


AMSO, AL Set Screw Splice, 1/0-14 AWG, 2 Screws, Al/Cu Rated

By Burndy
Catalog # [AMSO](#)



Aluminum Mechanical Splice, 1/0-14 AWG, 7/16" Screw Dia, 2 Screws, Al/Cu Rated, Tin Plated.

Application

For Use With Copper And Aluminum Conductors

General

Catalog Number	AMSO
Connector Type	In-Line
EU RoHS Indicator	Yes
Hex Size	Slot
Installation Torque	50 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin
Sub Brand	SPLICER/REDUCER
Temperature Rating	194° F
Type	AMS, Dual Rated
UPC	781810241011
UPC 12 Digit	7818102410111

Dimensions

Dimension - H1 Height inch	0.75 in
Dimension - Height fraction	3/4
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.91 in
Dimension - Width fraction	3/4 in
Dimension - Width inch	0.75 in
Dimension - Width mm	19 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run	12 AWG;10 AWG;8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
------------------------	---

Conductor - AL Str Run Range	12 AWG-1/0 AWG
Conductor - AL Str Size	12 AWG;10 AWG;8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Size Range	12 AWG-1/0 AWG
Conductor - AL Str Tap	12 AWG;10 AWG;8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Tap Range	12 AWG-1/0 AWG
Conductor - Copper Solid Run	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - Copper Solid Run Range	14 AWG-1/0 AWG
Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - Copper Solid Size Range	12 AWG-1/0 AWG
Conductor - Copper Solid Tap	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - Copper Solid Tap Range	14 AWG-1/0 AWG
Conductor - Copper Str Run	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Run Range	14 AWG-1/0
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	14 AWG-1/0
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Tap Range	14 AWG-1/0

Conductor Size 14-1/0 AWG

Carton Quantity 360

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Product Assets

- [3D Models - AMSO_MODEL-IGES](#)
- [3D Models - AMSO_MODEL-STEP](#)
- [3D Models - AMSO_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_AMS_Lineart](#)
- [Sales Drawings - sd207208-01](#)
- [Specifications - AMSO](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-AMSO-SPEC-EN | REV 10/2024