

## TN1410, Nylon Ring Terminal For 16 - 14 AWG

By Burndy  
Catalog # TN1410

Copper Terminal, Ring Tongue, 16-14 AWG, #8-#10 Stud, 600 Volts Max., Nylon Insulated, Funnel Entry, Tin Plated.



### Features

- Integral one-piece copper barrel / insulation grip and wire strain relief design for improved physical strength characteristics over a multi-piece design
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Brazed seam provides a stronger barrel design, minimizes any possible splitting and eliminates folding
- Deep inner barrel serrations and smooth funnel entry for excellent conductivity and pullout strength values along with the easy wire insertion
- Insulation is locked in place, will not twist off, maintaining proper dielectric values
- Electro-tin plated for durable, long lasting resistance to identification
- Ring tongue provides a secure termination under the screw head that cannot be removed without complete removal of the screw, allowing two or more terminals to be stacked on a common stud

### Application

For Heavy Duty Industrial, Utility And Military Power And Control-Circuit Applications

### General

Catalog Number	TN1410
Color Code	Blue
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	INSULUG
Trade Name	INSULUG™

Type	Ring Tongue
UPC	781810734568

### Dimensions

Cable Insulation Diameter Maximum	0.153 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.89 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	7/32
Dimension - Stud Size inch	#8;#10
Dimension - Z (inch)	0.31 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Solid Size	16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Range	#14 AWG to #16 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity 1200  
Pallet Quantity 99999

## Product Assets

Catalogs - BURNDY Master Catalog - Section B - Small  
Compression  
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog  
Customer Notices - Prop 65 Notice  
Interactive Catalog - BURNDY Full-Line Digital Catalog  
Product Cross Section Image(s) - BUR\_TN186\_LineArt  
Sales Drawings - 50094155  
Specifications - TN1410



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_MX-TN1410-SPEC-EN | REV 10/2024