



BGBL250, Aluminum Lay-in Lug, 250 kcmil-#6, 7/16" Stud, Tin Plated

By Burndy
Catalog # [BGBL250](#)

Aluminum Lay-in Lug, 250 kcmil-#6 AWG, 7/16" Stud, Tin Plated.



Features

- UL486B Listed, AL9CU Rated for copper and aluminum conductor combinations up to 90°C, 600 Volt applications
- UL Recognized for grounding and bonding
- Lay-in feature eases installation

Application

For Copper And Aluminum Conductor Combinations Up To 90 DEG C, 600 Volt Applications

General

Catalog Number	BGBL250
EU RoHS Indicator	Yes
Hex Size	5/16
Installation Torque	180 LBS/in
Recommended in-lb	
Material	Aluminum
Material Type - Screw	Steel - Zinc Plated
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin
Sub Brand	QIKLUG
Temperature Rating	194
Trade Name	QIKLUG™
Type	BGBL, Lay-In
UPC	781810124819
UPC 12 Digit	7818101248199

Dimensions

Dimension - D inch	1.18 in
Dimension - Height fraction	1-4/5 in
Dimension - Height inch	1.79 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.20 in
Dimension - N inch	0.4 in
Dimension - Pad Width inch	0.80 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - AL Str Size Range	6 AWG-250 kcmil
Conductor - Copper Solid Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	6 AWG-4/0 AWG
Conductor - Copper Str Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	6 AWG-250 kcmil
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size• CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-B
Standards - Industry Standards Met	UL 486A-B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	175
-----------------	-----

Product Assets

[3D Models - BGBL250_MODEL-IGES](#)
[3D Models - BGBL250_MODEL-PDF](#)
[3D Models - BGBL250_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BGBL250_LineArt](#)
[Sales Drawings - SE..212385-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-BGBL250-SPEC-EN | REV 8/2024