

GA25H29, Mechanical Ground Connector for Copper Cable to H-Beam

By Burndy
Catalog # [GA25H29](#)



Mechanical Ground Connector for Copper Cable to "H" Beam;
Accommodates: "H" Beam 1-7/8" - 2-1/2" x 2-1/2"; 2/0 Solid - 250 kcmil Copper

Features

- High copper alloy ground connector
- Joins wide range of cable parallel to "H" beams or square tube
- Silicon bronze for superior corrosion protection

General

Catalog Number	GA25H29
Installation Torque	240 Lb in
Recommended Run in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
UPC	781810001899
UPC 12 Digit	7818100018999

Dimensions

Dimension - Height fraction	4-3/4 in
Dimension - Height inch	4.75 in
Dimension - Width inch	4 in
Dimension - Width mm	102 mm

Conductor Related

Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Solid Size Range	2/0 Sol. - 250 kcmil
Conductor - Copper Str Size	250 kcmil
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_gahla](#)
- [Sales Drawings - SC29935-01_2](#)
- [Specifications - GA25H29](#)