



YCHC29TC29, Cu Compression C Tap, 250 kcmil-2 AWG Run and Tap

By Burndy
Catalog # [YCHC29TC29](#)



Copper Compression C Tap, 250 kcmil- 2 AWG (Main), 250 kcmil- 2 AWG (Tap), Tin Plated.

Application

Wire Tap

General

Catalog Number	YCHC29TC29
Color Code	Orange
Connector Type	C-TAP
Die Index	997
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YCHC Series
UPC	781810013717
UPC 12 Digit	7818100137177

Dimensions

Dimension - Height inch	2.12 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.94 in
Dimension - Strip Length inch	1 in
Dimension - Width inch	0.98 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Flex I Run	2 AWG-4/0 AWG Range
Conductor - Copper Flex I Tap	2 AWG-4/0 AWG Range
Conductor - Copper Flex K Run Range	2 AWG-4/0 AWG
Conductor - Copper Flex K Tap Range	2 AWG-4/0 AWG
Conductor - Copper Flex M Run Range	2 AWG-4/0 AWG
Conductor - Copper Flex M Tap Range	2 AWG-4/0 AWG
Conductor - Copper Str Run	250 KCMIL-2 AWG
Conductor - Copper Str Run Range	250 KCMIL-2 AWG
Conductor - Copper Str Tap	250 KCMIL-2 AWG
Conductor - Copper Str Tap Range	250 KCMIL-2 AWG
Conductor - Material	COPPER
Conductor Size	250 KCMIL-250 KCMIL
Conductor Type	CODE/FLEX

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	24
Pallet Quantity	9408

Product Assets

[3D Models - YCHC29TC29_MODEL-IGES](#)
[3D Models - YCHC29TC29_MODEL-STEP](#)
[3D Models - YCHC29TC29_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..206624-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YCHC29TC29-SPEC-EN | REV 6/2024