

YDS8W, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # YDS8W



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: #8 Cu Sol (Hard, Medium, or Soft Drawn), Die Index: 171, Made of copper tubing, Installed with standard tools and dies.

Application

For Solid Copper Conductors

General

Catalog Number	YDS8W
Connector Type	Splice
Construction Material - Main	Copper
Die Index	171
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of	1
Crimps Required	
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
Type	YDS-W
UPC	781810820957

Dimensions

Dimension - B Length inch	0.70 in
Dimension - L Length Overall mm	42 mm
Dimension - Length Overall inch	1.65 in
Dimension - Outside Diameter inch	0.25 in

Conductor Related

Conductor - Copper Solid Size 8 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity 100

Product Assets

- [3D Models - YDS8W_MODEL-STEP](#)
- [3D Models - YDS8W_MODEL-PDF](#)
- [3D Models - YDS8W_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YDS_LineArt](#)
- [Sales Drawings - SD..015142-02](#)
- [Specifications - YDS8W](#)