

## YGHR26C34 Figure 8 Compression Ground Rod Connector

By Burndy  
Catalog # YGHR26C34



Copper Compression Connector, 2 AWG(Str)-2/0 AWG(Str), 3/4" Ground Rod.

### Features

- High torque strength ground rod connector accepts a wide range of copper conductors to ground rod
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

### Application

For Direct Burial In Earth Or Concrete

### General

Catalog Number	YGHR26C34
Connector Type	Tap
Die Index	998;1012
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of	1
Crimps Required	
Plated	N
Plating Type	Unplated
Precrimp Die	UPRECRIMP58
Prefilled Oxide Inhibitor	Y
Sub Brand	HYGROUND, HYTAIL
Trade Name	HYTAIL™
Type	Taps
UPC	781810220726
UPC 12 Digit	7818102207266

### Dimensions

Dimension - B Length fraction	22/25 in
Dimension - B Length inch	0.88 in
Dimension - Ground Rod Size	3/4
Dimension - Height fraction	2-15/79 in
Dimension - Height inch	2.19 in
Dimension - Height mm	55.6 mm
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

### Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	2 AWG-2/0 AWG
Conductor - Rod Size	3/4 in
Conductor - Rod Size Range	3/4 in
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size A</li> <li>• Rod-Size B</li> </ul>

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL467</li> <li>• IEEE 837</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL467</li> <li>• IEEE 837</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	20
Pallet Quantity	4640

### Product Assets

[3D Models - YGHR26C34\\_MODEL-PDF](#)  
[3D Models - YGHR26C34\\_MODEL-IGES](#)  
[3D Models - YGHR26C34\\_MODEL-STEP](#)  
[Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YGHR-C\\_LineArt](#)  
[Sales Drawings - sd..088266-01](#)  
[Specifications - YGHR26C34](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_MX-YGHR26C34-SPEC-EN | REV 10/2024