

KPA4CUNPL, Mechanical Pressure Bar Style Copper Lug, #14 Sol-#4 Str, 1-Hole

By Burndy
Catalog # [KPA4CUNPL](#)



SCRULUG™ Mechanical Terminal for Copper Cable; 1-Hole;
Accommodates: #14 Sol - #4 Str; 1.20" Length; .50" Width

Features

- High copper alloy terminal (unplated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Application

For Joining A Wide Range Of Cable To Equipment Pads Or Terminal Blocks, Especially Good In Light Industrial Applications

General

Catalog Number	KPA4CUNPL
Connector Type	Pressure Bar
EU RoHS Indicator	Yes
Installation Torque	35
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	N
Plating Type	Unplated
Sub Brand	SCRULUG
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810006245

Dimensions

Dimension - Bolt Size fraction	1/4
Dimension - D inch	0.59 in
Dimension - Height fraction	47/50 in
Dimension - Height inch	0.94 in
Dimension - Height mm	23.9 mm
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	31

Dimension - Length Overall inch	1.22
Dimension - N inch	0.3 in
Dimension - Pad Width inch	0.50 in
Dimension - Stud Size inch	1/4
Dimension - Width inch	0.42 in
Dimension - Width mm	11 mm

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Navy Size	23 (7) Navy;30 (19) Navy;40 (19) Navy
Conductor - Copper Str Navy Size Range	23 (7) Navy-40 (19) Navy
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG
Conductor Size	14-4 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity 100
Pallet Quantity 59400

Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_KPA_Lineart
Sales Drawings - SC..011842-01
Specifications - KPA4CUNPL

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-KPA4CUNPL-SPEC-EN | REV 10/2024