

## YSM8C, Uninsulated Parallel Splice For 6,088 - 16,864 cmils

By Burndy  
Catalog # YSM8C



Copper Compression Parallel Splice, 6088-16864 Circular Mil,  
0.41" Splice Length, Short Barrel, Tin Plated.

### Features

- Seamless tubing
- Beveled barrel for ease of wire entry
- Tin plated
- Parallel design results in only one crimp necessary
- Uninsulated barrel provides an economical termination solution when insulation is not specified

### Application

HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling

### General

Catalog Number	YSM8C
Connector Type	Parallel Splice
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Temperature Rating	90
Trade Name	HYLINK™
Type	YSM
UPC	781810805794
UPC 12 Digit	7818108057944

### Dimensions

Dimension - Length Overall inch	0.41 in
------------------------------------	---------

Dimension - Outside Diameter  
inch

Dimension - Strip Length inch

### Conductor Related

Conductor - Copper Str Size

12 AWG;10 AWG;9 AWG;8  
AWG

Conductor - Copper Str Size  
Range

12 AWG-8 AWG

Conductor Size

6,088 - 16,864 cmils

Conductor Type

- CU C Solid-Size
- CU C Str-Size

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	200
-----------------	-----

### Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small  
Compression](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - 50094200](#)

[Specifications - YSM8C](#)