

KVS34, 2-piece Service Connector with neoprene rings

By Burndy
Catalog # [KVS34](#)



Compact, two-piece, high strength, high copper alloy BURNDY OKLIP recommended for heavy duty connections. Neoprene rings hold DURIIUM bolts in place during installation. Installed with ordinary wrench. Recommended tightening torque: 375 in-lb.

Application

For Copper, Copperweld

General

Catalog Number	KVS34
EU RoHS Indicator	Yes
Installation Torque	375 LBS/in
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	OKLIP
Trade Name	OKLIP™
Type	KVS, Compact
UPC	781810063200
UPC 12 Digit	7818100632000

Dimensions

Dimension - Height inch	2.65 in
Dimension - Height mm	67.31 mm
Dimension - Stud Size inch	1/2 in
Dimension - Width inch	2.20 in

Conductor Related

Conductor - Copper Str Run Range	400 kcmil - 500 kcmil
Conductor - Copper Str Tap Range	10 str. - 500 kcmil

Conductor Type

- CU C Str-Run
- CU C Str-Tap
- CU Weld C Solid-Run
- CU Weld C Solid-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486C
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

- [3D Models - KVS34_MODEL-IGES](#)
- [3D Models - KVS34_MODEL-PDF](#)
- [3D Models - KVS34_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_KVS_Lineart](#)
- [Sales Drawings - SC..052062-01](#)
- [Specifications - BURNDY_KVS34_Specsheet](#)
- [Specifications - KVS34](#)