


KVSW28, Mechanical Connector with Spacer Bar

By Burndy
Catalog # [KVSW28](#)



Mechanical Connector For CUWeld and Copper Supplied with a CU alloy Spacer that separates run and tap conductors, Recommended Torque: 250 LBS.

Features

- Compact, 2-piece, high strength, high copper alloy, recommended for heavy duty connections
- High copper alloy spacer bar separates run and tap conductors
- Provides high contact pressure, confines conductor strands and assures vibration-proof connection
- Longer peened bolt permits swivel action for easier installation
- Neoprene rings hold silicon bronze bolts in place during installation
- Installed with ordinary wrench

Application

For Copper And Copperweld Conductors

General

Catalog Number	KVSW28
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	OKLIP
Trade Name	OKLIP™
Type	KVSW
UPC	781810066553
UPC 12 Digit	7818100665533

Dimensions

Dimension - Height inch	2.50 in
Dimension - Height mm	63.50 mm
Dimension - Length Overall inch	1.04 in
Dimension - Stud Size inch	3/8 in

Dimension - Width inch 1.67 in

Conductor Related

Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-4/0 AWG
Conductor - Copper Str Run	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	1/0 str. - 4/0 str.
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	6 sol. - 4/0 str.
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KVSW_LineArt](#)
[Sales Drawings - sd009323-01](#)
[Specifications - KVSW28](#)