



Locking Devices, Bryant Power Interrupting, Industrial, Flanged Inlet, 60A 600V AC, 4-Pole 5-Wire Grounding, Non- NEMA, Screw Terminal, Blue

By Bryant
Catalog # 26522



Locking Devices, Bryant Power Interrupting, Industrial, Flanged Inlet, 60A 600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Steel housing

Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Color coded metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with stainless steel terminal screws provide maximum termination strength and dependability

Application

Extra Heavy Duty Industrial

General

Color	Blue
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	60A Single Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Style	Grounding
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786574229

Dimensions

Dimensions	4.12 in x 4.12 in x 3.95 in
Display Size	Standard Sized Product
Height	3.95 in
Length	4.12 in
Width	4.12 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current Rating	60 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	600 VAC
Voltage Rating Description	600V AC

Conductor Related

Number Of Wires	5-Wire
Wire Size	#18 AWG to #8 AWG

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - Bryant H-26 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[26516 - Locking Devices, Bryant Power Interrupting, Industrial, Female Connector Body, 60A 600V AC, 4-Pole 5-Wire Grounding, Non-NEMA, Screw Terminal, Blue](#)



A proud member of the Hubbell Family.