



Full Cycle Ratchet Crimper, #8-18 AN Copper #10-22 Sol, #8-22 Str

By Burndy
Catalog # [MR89Q](#)



Full Cycle Ratchet Crimper, #8-18 AN CU #10-22 Sol, #8-22 Str.

Application

Crimping

General

Application - For Use On	Uninsulated Terminals and Splices
Catalog Number	MR89Q
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
Type	Crimper
UPC	781810786031
UPC 12 Digit	781810786031

Dimensions

Dimensions	11.00 in x 2.76 in x 0.88 in
Height	0.88 in
Length	11 in
Weight	1.5 lb

Width 2.76 in

Conductor Related

Crimping Ranges #18 - #8 AN, #22 - #8 AWG

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Package Contents Tool only

Product Assets

[Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_MR8_LineArt](#)
[Sales Drawings - sd041872-01](#)
[Specifications - MR89Q](#)