



PENA134, Oxide Inhibitor, 4 ounce

By Burndy
Catalog # [PENA134](#)

Oxide Inhibiting Electrical Joint Compound, 4 OZ, For Al-Al, Al-Cu & Al Conduit Threads / Insulated Cable.



Application

Aluminum to Aluminum, Aluminum to Conduit, Aluminum to Copper

General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	PENA134
Container Type	Squeeze Bottle
EU RoHS Indicator	Yes
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
Type	Sealing compound
UPC	781810593127
UPC 12 Digit	7818105931277
Viscosity at 100 Fahrenheit	250 °F

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Container Size	4 oz
----------------	------

Product Assets

- [3D Models - PENA134_MODEL-PDF](#)
- [3D Models - PENA134_MODEL-IGES](#)
- [3D Models - PENA134_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_PENA134_LineArt](#)
- [Sales Drawings - sc087704-01](#)
- [SDS - PENETROX A-13 ESPANOL SDS](#)
- [SDS - PENETROX A-13 PORTUGUESE SDS](#)
- [SDS - PENETROX A-13 GERMAN SDS](#)
- [SDS - PENETROX A-13 SDS](#)
- [SDS - PENETROX A-13 ITALIAN SDS](#)
- [SDS - PENETROX A-13 FRENCH SDS](#)