



Locking Devices, Locking Devices, Industrial, Flanged Inlet, 50A 250V DC/600V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Galvanized

By Bryant
Catalog # 3767



Locking Devices, Industrial, Flanged Inlet with Lift Cover and Gasket, 50A 250V DC/600V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Steel Casing

General

Application	Extra Heavy Duty Industrial
Catalog Number	3767
Color	Metallic
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	50A Male Flanged Inlet-For Replacement Use
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786652705

Dimensions

Dimensions	2.77 in x 3.50 in x 3.50 in
Display Size	Standard Sized Product
Height	3.5 in
Length	2.77 in
Width	3.5 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC
Wattage	

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY H-22 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-3767-SPEC-EN | REV 6/2024