



Locking Devices, Locking Devices, Industrial, Flanged Inlet, 50A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Galvanized

By Bryant
Catalog # 3768



Locking Devices, Industrial, Flanged Inlet with Lift Cover and Gasket, 50A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Steel Casing

Features

- Flanged Inlet with Lift Cover and Gasket
- 50A 250V DC/600V AC
- 3-Pole 4-Wire Grounding
- Non-NEMA
- Screw Terminal

Application

Extra Heavy Duty Industrial

General

| | |
|------------------------------|------------------------------------------------------------------------|
| Catalog Number | 3768 |
| Color | Metallic |
| EU RoHS Indicator | No |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Insulation | Insulated Body |
| Item Type | 50A Male Flanged Inlet-For Replacement Use |
| Material | Composite |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 3-Pole |
| OEM Brand Name | Hubbell Bryant |
| Style | Extra Heavy Duty |
| Temperature Rating | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact |
| Type | Flanged Inlet |

UPC

781786652750

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 2.77 in x 3.50 in x 3.50 in |
| Display Size | Standard Sized Product |
| Height | 3.5 in |
| Length | 2.77 in |
| Width | 3.5 in |

Electrical Ratings

| | |
|----------------------------|-----------------------------|
| Amperage Rating | 50 A |
| Connectivity | Pressure Terminal Screws |
| Current Rating | 50 A |
| Dielectric Strength | Withstands 3000V Minimum in |
| Voltage Rating | 250 VDC/600 VAC |
| Voltage Rating Description | 250 VDC/600 VAC |

Conductor Related

| | |
|-----------------|-------------------|
| Number Of Wires | 4-Wire |
| Wire Size | #18 AWG to #8 AWG |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 5 |
|-----------------|---|

Product Assets

[Catalog Page - BRY H-22 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 3768](#)