


SP10, Vinyl Splice For 12 - 10 AWG

By Burndy
Catalog # SP10



Copper Splice, 12-10 AWG, 1.23" Splice Length, Vinyl Insulated.

Features

- Manufactured from seamless electrolytic copper tubing to provide maximum conductivity and tensile strength in a high quality design with no seams to split
- Funnel entry for easy wire insertion
- Electro-tin plating provides durable, long lasting resistance to corrosion

Application

For Accommodating A Broad Range Of 600 Volt Cables

General

Catalog Number	SP10
Color Code	Yellow
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Polyvinylchloride
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	VINYLINK
Temperature Rating	105° C
Trade Name	VINYLINK™
Type	SP
UPC	781810710012
UPC 12 Digit	7818107100122

Dimensions

Cable Insulation Diameter Maximum	0.26 in
Dimension - Diameter Max Size inch	0.26 in
Dimension - L Length Overall mm	31 mm
Dimension - Length Overall inch	1.23 in

Dimension - Outside Diameter inch	0.26 in
Dimension - Strip Length inch	21/64 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 - 10 AWG
Conductor Size	12 - 10 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	480
Pallet Quantity	99999

Product Assets

- [3D Models - SP10_MODEL-PDF](#)
- [3D Models - SP10_MODEL-STEP](#)
- [3D Models - SP10_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_KTFBS_LineArt](#)
- [Sales Drawings - 50094190](#)
- [Specifications - SP10](#)