

TN1414F, Nylon Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [TN1414F](#)



Nylon Fork Terminal For 16 - 14 AWG.

Application

Power Connector

General

Catalog Number	TN1414F
Color Code	Blue
Connector Type	Fork Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	TN-F
UPC	781810733240

Dimensions

Cable Insulation Diameter Maximum	0.153 in
Dimension - Bolt Size fraction	1/4
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.03 in
Dimension - Pad Width inch	0.47 in
Dimension - Strip Length inch	7/32
Dimension - Stud Size inch	1/4
Dimension - Z (inch)	0.38 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Range	#14 AWG to #16 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Pallet Quantity	99999

Product Assets

- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_yaesfla](#)
- [Sales Drawings - 50094172](#)
- [Specifications - TN1414F](#)