



Locking Devices, Locking Devices, Industrial, Flanged Inlet, 15A 125V, 2-Pole3-Wire Grounding, L5-15P, Screw Terminal, White

By Bryant
Catalog # 4716MB



Locking Devices, Industrial, Flanged Inlet, 15A 125V, 2-Pole3-Wire Grounding, L5-15P, Screw Terminal, White

Features

- Flanged Inlet
- 15A 125V
- 2-Pole3-Wire Grounding
- L5-15P
- Screw Terminal

Application

Extra Heavy Duty Industrial

General

Catalog Number	4716MB
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786405202

Dimensions

Dimensions	1.84 in x 2.50 in x 1.68 in
Display Size	Standard Sized Product
Height	1.68 in
Length	1.84 in
Width	2.5 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current Rating	15 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	125 V
Voltage Rating Description	125V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Nema Rating	L5-15P
-------------	--------

Logistics

Carton Quantity	10
Pallet Quantity	2080

Product Assets

- [Catalog Page - BRY H-6 Catalog Page](#)
- [Catalog Page - BRY Q-19 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 4716MB](#)