



Locking Devices, Locking Devices, Industrial, Flanged Inlet, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15P, Screw Terminal, White

By Bryant
Catalog # 4786MB



Locking Devices, Industrial, Flanged Inlet, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15P, Screw Terminal, White

Features

- Flanged Inlet
- 15A 277V AC
- 2-Pole 3-Wire Grounding
- L7-15P
- Screw Terminal

Application

Extra Heavy Duty Industrial

General

Catalog Number	4786MB
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786405301

Dimensions

Dimensions 1.84 in x 2.50 in x 1.68 in

Display Size	Standard Sized Product
Height	1.68 in
Length	1.84 in
Width	2.5 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current Rating	15 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	277 VAC
Voltage Rating Description	277V AC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Nema Rating	L7-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY H-6 Catalog Page](#)
- [Catalog Page - BRY Q-19 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 4786MB](#)

