



Disconnect Switches, Double Pole, 40A 600V AC, Black

By Bryant
Catalog # 50002D

Disconnect Switches, Double Pole, 40A 600V AC, Black



General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Open Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2 Pole
OEM Brand Name	Hubbell Bryant
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Standard Toggle
Style	Motor Controller/Disconnect
Type	Side Wire
UPC	781786631670

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	30000

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant E-12 Catalog page](#)
[Catalog Page - Bryant G-6 Catalog page](#)
[Catalog Page - Bryant G-2 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Literature - General Literature - Motor Controllers and Disconnects](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-50002D-SPEC-EN | REV 5/2023