

UCK1UL, Tin-Plated Cast Copper Alloy Interlocking-Finger Design Parallel Clamp

By Burndy
Catalog # [UCK1UL](#)



Interlocking finger design accommodates large range of conductor sizes. Tin-plated, cast of high copper alloy and clamped with silicon bronze DURUM bolt, wrench size: 1/2.

Features

- Tin-plated cast copper alloy featuring interlocking-finger design
- Accommodates large range of conductor sizes
- Clamped with silicon bronze bolts

Application

For Use With Aluminum Or Galvanized Steel Strand To Copper Or Copper Bonded Steel Wire, Grounding For The Cable TV Industry

General

Catalog Number	UCK1UL
EU RoHS Indicator	Yes
Installation Torque	180 LBS/in
Recommended in-lb	
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TAPIT
Type	UC-K, Universal
UPC	781810120750
UPC 12 Digit	7818101207500

Dimensions

Dimension - Height fraction	1-7/16 in
Dimension - Height inch	1.4375 in
Dimension - Height mm	36.5 mm
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1 in

Dimension - Width fraction	1-7/16 in
Dimension - Width inch	1.4375 in
Dimension - Width mm	37 mm

Conductor Related

Conductor - Copper Solid Size B	6 Sol
Conductor - Copper Str Size B	6 Str
Conductor - Galvanized Steel Str Size Range	1/4 in -5/16 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

- [3D Models - UCK1UL_MODEL-STEP](#)
- [3D Models - UCK1UL_MODEL-PDF](#)
- [3D Models - UCK1UL_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_UCK_LineArt](#)
- [Sales Drawings - SD..210746-01](#)
- [Specifications - UCK1UL](#)