

YAK34A2G1, Aluminum - Compression Stacking Terminal (HYLUG Terminal)



By Burndy
Catalog # [YAK34A2G1](#)

Cast Al Offset Stacking Lug, 2-NEMA Holes, 500 kcmil Al, 500 kcmil Al Compressed, 0.56" Hole Dia

General

Catalog Number	YAK34A2G1
Connector Type	Terminal
Die Index	317;705
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810802274
UPC 12 Digit	7818108022744

Dimensions

Dimension - B Length inch	2.41 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - D inch	3.06 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	197 mm
Dimension - Length Overall inch	7.75 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.25 in

Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2-1/2 in
Physical Attribute - Tongue Angle	Offset

Conductor Related

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YAK-A-2G_LineArt](#)
- [Sales Drawings - SD59493-01](#)
- [Specifications - YAK34A2G1](#)