

YGS28 Compression Grounding Splice, 4/0 AWG Cu

By Burndy
Catalog # YGS28



HYGROUND® Grounding Irreversible Compression Splice;
Accommodates: 4/0 str.

Features

- Irreversible compression ground splices specifically designed for grounding applications
- Each conductor element has an inspection probe hole and a center stop to ensure proper cable insertion
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Application

For Direct Burial In Earth Or Concrete

General

Catalog Number	YGS28
Connector Type	Splice
Die Index	15
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of	2
Crimps Required	
Plated	N
Plating Type	Unplated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splices
UPC	781810220429
UPC 12 Digit	7818102204299

Dimensions

Dimension - B Length fraction	1-7/20 in
Dimension - B Length inch	1.57 in
Dimension - L Length Overall mm	86 mm
Dimension - Length Overall inch	3.37 in
Dimension - Outside Diameter inch	0.69 in

Physical Attribute - Tongue Angle Straight

Conductor Related

Conductor - Copper Str Size	4/0 Str.
Conductor - Copper Str Size Range	4/0 Str.
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • UL 486A-486B • UL 486A-486B • UL467
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	10
Pallet Quantity	9600

Product Assets

- [Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YGS_LineArt](#)
- [Sales Drawings - SD..082514-01](#)
- [Specifications - YGS28](#)