



# Locking Devices, Industrial, Flanged Inlet, 20A 125/250V, 3-Pole 3-Wire Non-Grounding, L10-20P, Screw Terminal, White

By Bryant  
Catalog # 71020MB



Locking Devices, Industrial, Flanged Inlet, 20A 125/250V, 3-Pole 3-Wire Non-Grounding, L10-20P, Screw Terminal, White.

## Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

## Application

Extra Heavy Duty Industrial

## General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786692466

## Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Dielectric Strength	Withstands 3000V Minimum
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250V AC

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications and Compliance

Nema Rating	L10-20P
-------------	---------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Bryant H-9 Catalog page](#)  
[Catalog Page - Bryant Q-19 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-71020MB-SPEC-EN | REV 5/2023