



Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 30A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # 20403

Locking Devices, Bryant Power Interrupting, Industrial, Single Receptacle, 30A 600V AC/ 20A 250V DC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black, For F.S. and F.D. boxes



Application

- Extra Heavy Duty Industrial Specification Grade

General

| | |
|------------------------------|---|
| EU RoHS Indicator | No |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | 20A/30A Single Receptacle |
| Material | Composite |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 3-Pole |
| OEM Brand Name | Hubbell Bryant |
| Style | Grounding |
| Type | <ul style="list-style-type: none">• Receptacle• Receptacle |
| UPC | 781786618473 |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.28 in x 1.94 in x 1.75 in |
| Display Size | Standard Sized Product |
| Height | 1.75 in |
| Length | 3.28 in |
| Width | 1.94 in |

Electrical Ratings

| | |
|----------------------------|-----------------|
| Amperage Rating | 20A/30 A |
| Connectivity | Terminal Screws |
| Current Rating | 20A/30 A |
| Phase | Single Phase |
| Voltage Rating | 250 VDC/600 VAC |
| Voltage Rating Description | 250 VDC/600 VAC |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 4-Wire |
| Wire Size | #14 AWG to #10 AWG |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 20 |
|-----------------|----|

Product Assets

[Catalog Page - BRY H-25 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.