



Locking Devices, Industrial, Flanged Inlet, 20A 3-Phase Delta 480V AC, 3-Pole 3-Wire Non-Grounding, L12-20P, Screw Terminal, White

By Bryant
Catalog # 71220MB



Locking Devices, Industrial, Flanged Inlet, 20A 3-Phase Delta 480V AC, 3-Pole 3-Wire Grounding, L12-20P, Screw Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

General

Application	Extra Heavy Duty Industrial
Catalog Number	71220MB
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786694163

Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Dielectric Strength	Withstands 3000V Minimum
Voltage Rating	3 Phase 480 VAC
Voltage Rating Description	3 Phase 480V AC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L12-20P
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY Q-19 Catalog Page](#)
[Catalog Page - BRY H-9 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-71220MB-SPEC-EN | REV 6/2024