



Locking Devices, Bryant Power Interrupting, Industrial, Female Connector Body, 20A 125V/10A 250V DC 480V AC, Non-NEMA

By Bryant
Catalog # 23002G



Locking Devices, Bryant Power Interrupting, Industrial, Female Nylon Connector Body, 20A 125V AC or DC/10A 250V DC 480V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

Application

Heavy Duty Industrial

General

Catalog Number	23002G
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	10A/20A Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Grounding
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786618831

Dimensions

Dimensions	1.62 in x 1.62 in x 3.56 in
Display Size	Standard Sized Product
Height	3.56 in
Length	1.62 in
Width	1.62 in

Electrical Ratings

Amperage Rating	10A/20 A
Connectivity	Pressure Terminal Screws
Current Rating	10A/20 A
Voltage Rating	125 VAC/125 VDC/250 VDC/480 VDC
Voltage Rating Description	125 VAC/125 VDC/250 VDC/480 VDC

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#16 AWG to #12 AWG

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalog Page - BRY H-24 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 23002G](#)