



Locking Devices, Industrial, Flanged Inlet, 15A 125V, 2-Pole 2- Wire Non-Grounding, L1-15P, Screw Terminal, White

By Bryant
Catalog # 7523



Locking Devices, Industrial, Flanged Inlet, 15A 125V, 2-Pole 2-
Wire Non-Grounding, L1-15P, Screw Terminal, White

Application

Extra Heavy Duty Industrial

General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786629103

Dimensions

Dimensions	2.56 in x 2.19 in x 1.78 in
Display Size	Standard Sized Product
Height	1.78 in
Length	2.56 in
Width	2.19 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current Rating	15 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	125 V
Voltage Rating Description	125V

Conductor Related

Number Of Wires	2-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Nema Rating	L1-15P
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Bryant H-5 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

[7535 - Locking Devices, Industrial, Receptacle, 15A 125V, 2-Pole 2-Wire Non-Grounding, L1-15R, Screw Terminal, Black](#)
[7548 - Locking Devices, Industrial, Male Plug, 15A 125V, 2-Pole 2-Wire Non Grounding, L1-15P, Screw Terminal, Black](#)
[SS7 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 1.40" Opening, Standard Size, Stainless Steel](#)
[RW57300 - Wallplates and Boxes, Weatherproof Hood, 1-Gang, Multi Opening, Vertical, Gray](#)
[7540 - Locking Devices, Industrial, Duplex Receptacle, 15A 125V, 2-Pole 2-Wire Non Grounding, L1-15R, Screw Terminal, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-7523-SPEC-EN | REV 7/2023