



Locking Devices, Industrial, Flanged Inlet, 15A 125V/10A 250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # 7556MB



Locking Devices, Industrial, Flanged Inlet, 10A 250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black

Features

- Flanged Inlet
- 10A 250V
- 3-Pole 3-Wire Non-Grounding
- Non-NEMA
- Screw Terminal

Application

Extra Heavy Duty Industrial

General

Catalog Number	7556MB
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	10A Triple Gripper Flanged Inlet Non-NEMA
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786405356

Dimensions

Dimensions	1.84 in x 2.38 in x 1.68 in
Display Size	Standard Sized Product
Height	1.68 in
Length	1.84 in
Width	2.38 in

Electrical Ratings

Amperage Rating	10 A
Connectivity	Screw Terminals
Current Rating	10 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	250 V
Voltage Rating Description	250V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY H-15 Catalog Page](#)
- [Catalog Page - BRY Q-19 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 7556MB](#)