



# Straight Blade Devices, HI-VIS, Commercial Grade, Female Connector, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Hi-Visibility Orange

By Bryant  
Catalog # 5159HVO



Straight Blade Devices, HI-VIS, Commercial Grade, Female Connector, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Single Pack, Hi-Visibility Orange

## Features

- Commercial Grade
- Female Connector
- Straight
- 2-Pole 3-Wire Grounding
- 15A 125V

## Application

Heavy Duty

## General

Catalog Number	5159HVO
Color	Hi-Viz Orange
Cord Range	0.245"-0.655"
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Female Connector
Material	Thermoplastic
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786515901

## Dimensions

Display Size	Standard Sized Product
Weight	0.15 lb

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

## Conductor Related

Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
Pallet Quantity	168

## Product Assets

[Catalog Page - BRY A-22 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 5159HVO](#)

